## Optimal Settings for Spinnaker Pressure Sensitive Press: <u>Ricoh</u> C901+, C7100, C9110 "A" List Approved Media

	ed*	Typical Values		Settings Used				
	irm.			GSM Range				
Item	Kicon Tested & Confirmed*	GSM	Caliper (mils)	Paper Type	** R901+	C7100	C9110	Comments
DiversiPrint <sup>®</sup> 60# Gloss				Coated				Maximum of 432
Permanent		198	8.1	Glossy	7	163-220		sheets on
58# Scored Liner				Glossy				Finisher Tray
DiversiPrint <sup>®</sup> 60# Gloss				Coated				Maximum of 410
Removable		209	8.1	Glossy	5			sheets on
58# Scored Liner				Glossy				Finisher Tray
DiversiPrint <sup>®</sup> 55# Semi Gloss				Coated				Maximum of 432
Permanent		193	7.0	Glossy	6			sheets on
58# Scored Liner				Glossy				Finisher Tray
DiversiPrint® 60# Ultra Matte™				Coated				Maximum of 423
Permanent		202	8.1	Matte	5			sheets on
58# Scored Liner				Walle				Finisher Tray
DiversiPrint® 60# Ultra Matte™				Coated				Maximum of 390
Removable		213	8.1	Matte	5			sheets on
58# Scored Liner				Watte				Finisher Tray
DiversiPrint <sup>®</sup> 60# Ultra Matte™ Cover-Up				Coated				Maximum of 404
Permanent		210	8.1	Matte	5			sheets on
58# Scored Liner				Walle				Finisher Tray
DiversiPrint <sup>®</sup> 60# Bright White				Plain or				Maximum of 423
Permanent		202	8.3	Coated		163-220	189	sheets on
58# Scored Liner				Matte				Finisher Tray
Matte White Digital Vinyl					not teconmender	256-300, 5th	not recommender	
Permanent		273	8.9	Matte	comme	color station on	comme	
80# Liner					noties	low speed @ 180°	notree	
Matte White Digital Vinyl					not econmender	<b>256-300,</b> 5th	not recommender	Maximum of 297
Removable	Х	270	8.8	Matte	comme	color station on	omme	sheets on
80# Liner					notree	low speed @ 180°	NOTIE	Finisher Tray
DiversiPrint <sup>®</sup> Digital Satin Cloth								
Permanent		262	11.6	Glossy Textured		220-256		
80# Scored Liner				rextured				
All materials tested were 12x18 sheets								

All materials tested were 12x18 sheets.

^ Indicates GSM and caliper value for removable adhesive item.

\*\* For Ricoh 901+ testing, the speed setting for all materials was 100%. No advanced settings were used. For all materials, the media can only be fed from Trays 3 and 4.

Printers may vary. Refer to owner's manual for specific details.

Updated 02/22/19



800.543.9452 Technical Consulting: 877.210.5104 spinps.com sales@spinps.com